

#### Construction

The 2/2-way metal tank bottom valve GEMÜ 643 is manually operated with a side mounted gear which has an optical position indicator as standard. The stainless steel valve body is machined from a single block (no welds) and is designed for welding directly into a tank bottom. The distance piece and the gearbox housing are made of stainless steel.

#### **Features**


- · Suitable for inert and corrosive\* liquid and gaseous media
- · CIP/SIP cleaning and sterilizing capabilities

### **Advantages**

- Tanks can be optimally drained, cleaned and sterilized by using the GEMÜ 643
- The temperature resistant plastic handwheel prevents burns injuries at high operating temperatures
- Compact design (ideal when space is at a premium)
- Tank bottom valve body also available with pneumatic or motorized actuator on request
- Bonnet can be rotated through 360°
- · Versions according to ATEX on request
- Handwheel shaft extension by the user is possible

\*see information on working medium on page 2

#### **GEMÜ 643**





#### **Technical data**

### Working medium

Corrosive, inert, gaseous and liquid media which have no negative impact on the physical and chemical properties of the body and diaphragm material.

Maximum permissible pressure of working medium, applied upstream

150 psi

### **Temperatures**

Media temperature 14 ... 212 °F

### Sterilisation temperature (1)

EPDM (Code 13)

max. 302 °F (2), max. 60 min per cycle

EPDM (Code 17)

max. 302 °F (2), max. 180 min per cycle

PTFE/EPDM (Code 54)

max. 302 °F (2), no time limit per cycle

PTFE/EPDM (Code 5M)

max. 302 °F (2), no time limit per cycle

<sup>1</sup> The sterilisation temperature is valid for steam (saturated steam) or superheated water.


the service life of the diaphragms will be reduced. In these cases, maintenance cycles must be adapted accordingly. This also applies to PTFE diaphragms exposed to high temperature fluctuations.

PTFE diaphragms can also be used as moisture barriers; however, this will reduce their service life.

The maintenance cycles must be adapted accordingly.

GEMÜ 555 and 505 globe valves are particularly suitable for use in the area of steam generation and distribution. The following valve arrangement for interfaces between steam pipes and process pipes has proven itself over time:

A globe valve for shutting off steam pipes and a diaphragm valve as an interface to the process pipes.



Ambient temperature

32 ... 140 °F

Nominal size	Bonnet	Operating pressure [psi]		Weight
[mm]	Code	EPDM	PTFE	[lbs]
15	2AT	0 - 150	0 - 150	6.6
20	2AT	0 - 150	0 - 150	6.6
25	2AT	0 - 150	0 - 150	6.6
32	3AT	0 - 150	0 - 150	13.2
40	3AT	0 - 150	0 - 150	13.2



 $<sup>^{2}</sup>$  If the sterilisation temperatures listed above are applied to the EPDM diaphragms for longer periods of time,

## Order data

Body configuration	Code
Tank valve body	В

Nominal size		Code
DN 15	NPS 1/2"	15
DN 20	NPS 3/4"	20
DN 25	NPS 1"	25
DN 32	NPS 1 1/4"	32
DN 40	NPS 1 1/2"	40

Diaphragm material	Code
EPDM	13
EPDM	17
EPDM	19
EPDM	36
PTFE/EPDM, two-piece	5M
Material complies with FDA requirements	

Control function	Code
Manually operated	0

Connection	Code
Butt weld spigots	
Spigots DIN	0
Spigots EN 10357 series B	
(formerly DIN 11850 series 1)	16
Spigot EN 10357 series A	
(formerly DIN 11850 series 2) / DIN 11866 series A	17
Spigots DIN 11850 series 3	18
Spigots SMS 3008	37
Spigot ASME BPE / DIN 11866 series C	59
Spigot ISO 1127 / EN 10357 series C /	
DIN 11866 series B	60
Spigots ANSI/ASME B36.19M Schedule 10s	63
Spigots ANSI/ASME B36.19M Schedule 5s	64
Spigots ANSI/ASME B36.19M Schedule 40s	65

Bonnet size		Code
Bonnet size 2AT	(DN 15 - 25)	2AT
Bonnet size 3AT	(DN 32 - 40)	3AT

Surface finish	Code
Code see page 4	

Valve body material	Code
1.4435 (F316L), forged body	40
1.4435 (BN2), forged body $\Delta$ Fe<0.5 $\%$	42

Order example	643	25	В	60	40	13	0	2AT	1503
Туре	643								
Nominal size		25							
Body configuration (code)			В						
Connection (code)				60					
Valve body material (code)					40				
Diaphragm material (code)						13			
Control function (code)							0		
Bonnet size (code)								2AT	
Surface finish (code see page 4)									1503



### Order data

### Internal surface finishes for forged bodies <sup>1</sup>

Pandings for Presson	Mechanical	ly polished <sup>2</sup>	Electropolished		
Readings for Process Contact Surfaces	Hygienic class DIN 11866	Code	Hygienic class DIN 11866	Code	
Ra ≤ 0,8 μm	H3	1502	HE3	1503	
Ra ≤ 0,6 μm	-	1507	-	1508	
Ra ≤ 0,4 µm	H4	1536	HE4	1537	
Ra ≤ 0,25 $\mu$ m <sup>3</sup>	H5	1527	HE5	1516	


Pandings for Process	Mechanicall	y polished <sup>2</sup>	Electropolished		
Readings for Process Contact Surfaces acc. to ASME BPE 2016 4	ASME BPE Surface Designation	Code	ASME BPE Surface Designation	Code	
Ra Max. = 0,76 μm (30 μinch)	SF3	SF3	-	-	
Ra Max. = 0,64 μm (25 μinch)	SF2	SF2	SF6	SF6	
Ra Max. = 0,51 μm (20 μinch)	SF1	SF1	SF5	SF5	
Ra Max. = 0,38 μm (15 μinch)	-	-	SF4	SF4	


<sup>&</sup>lt;sup>1</sup> Surface finishes of customized valve bodies may be limited in special cases.

Ra acc. to DIN EN ISO 4288 and ASME B46.1

## **Mounting position**

Mounting position (with handwheel shaft extension by user)







<sup>&</sup>lt;sup>2</sup> Or any other finishing method that meets the Ra value (acc. to ASME BPE).

 $<sup>^3</sup>$  The smallest possible Ra finish for 1/4" (DN 8) BS 4825 Part 1 and ASME BPE is 15  $\mu inch.$ 

<sup>&</sup>lt;sup>4</sup> When using these surfaces, the bodies are marked according to the specifications of ASME BPE. The surfaces are only available for valve bodies which are made of materials (e.g. GEMÜ material codes 40, 41, 44) and use connections (e.g. GEMÜ connection codes 59, 80, 88) according to ASME BPE.


# Dimensions [inch]

Butt weld spigots, connection code 0, 16, 17, 18, 60 Valve body material: Forged body (code 40)																
Pipe standard							DIN EN 1035 series (former DIN 118 series 1		es B nerly 1850	series A y (formerly DIN 11850		DIN 11850 Series 3		ISO 1127 / EN 10357 series C / DIN 11866 series B		
		Conn	ection	code			0 16		6	17		18		60		
MG	DN	А3	В3	øΒ	SP	С	ød	s	ød	S	ød	S	ød	S	ød	s
	15	6.54	4.09	4.72	0.24	0.98	0.709	0.059	0.709	0.039	0.748	0.059	0.787	0.079	0.839	0.063
25	20	6.54	4.09	4.72	0.24	0.98	0.866	0.059	0.866	0.039	0.906	0.059	0.945	0.079	1.059	0.063
	25	6.54	4.09	4.72	0.24	0.98	1.102	0.059	1.102	0.039	1.142	0.059	1.181	0.079	1.327	0.079
40	32	7.48	4.33	6.30	0.24	0.98	1.339	0.059	1.339	0.039	1.378	0.059	1.417	0.079	1.669	0.079
40	40	7.48	4.33	6.30	0.24	0.98	1.575	0.059	1.575	0.039	1.614	0.059	1.654	0.079	1.902	0.079

MG = diaphragm size

Butt weld spigots. connection code 37, 59, 63, 64, 65 Valve body material: Forged body (code 40)																
Pipe standard									ASME BPE / DIN 11866 series C		ANSI/ASME B36.19M Schedule 10s		ANSI/ASME B36.19M Schedule 5s		ANSI/ASME B36.19M Schedule 10s	
Connection code						37		59		63		64		65		
MG	DN	А3	В3	øΒ	SP	С	ød	S	ød	S	ød	S	ød	S	ød	S
	15	6.54	4.09	4.72	0.24	0.98	-	-	-	-	0.839	0.083	0.839	0.065	0.839	0.109
25	20	6.54	4.09	4.72	0.24	0.98	-	-	0.750	0.065	1.051	0.083	1.051	0.065	1.051	0.113
	25	6.54	4.09	4.72	0.24	0.98	0.984	0.047	1.000	0.065	1.315	0.109	1.315	0.065	1.315	0.133
40	32	7.48	4.33	6.30	0.24	0.98	1.327	0.047	-	-	1.661	0.109	1.661	0.065	1.661	0.14
40	40	7.48	4.33	6.30	0.24	0.98	1.496	0.047	1.500	0.065	1.902	0.109	1.902	0.065	1.902	0.145

MG = diaphragm size






Overview of valve bodies for GEMÜ 643													
		Spigots											
Connection code		0	16	17	18	37	59	60	63	64	65		
-	Material code		40	40	40	40	40	40	40	40	40		
MG	DN												
	15	Х	Х	Х	Х	-	-	Х	Х	Х	Х		
25	20	X	Х	Х	×	-	X	X	X	×	X		
	25	X	Х	Х	X	X	X	X	X	X	Х		
40	32	Х	Х	Х	Х	Х	-	Х	Х	Х	Х		
40	40	X	х	Х	X	X	x	×	X	X	Х		

Availability of material code 42: same as code 40 MG = diaphragm size



## Shaft extension (by user)



### Attention!

When the user installs a handwheel extension care should be taken that it has sufficient bearing points.

### **Torques for shaft extension:**

Bonnet size 2AT 97 in-lbs Bonnet size 3AT 124 in-lbs

For further metal diaphragm valves, accessories and other products, please see our Product Range catalogue and Price List.

Contact GEMÜ.



