



Integrated Sensing Platform (ISP)



ITT

ENGINEERED FOR LIFE

Integrated Sensing Platform (ISP) Overview

Intelligent Design Drives Reliable, High Performing Valve Sensing

The Integrated Sensing Platform (ISP) is the next generation of linear position sensing developed specifically for the toughest applications in the Biopharm and sanitary industries.

This ultra-compact sensing module is the result of Engineered Valves partnering with a recognized leader in valve communications and control. Combining Engineered Valves knowledge of valve design with cutting edge valve position feedback and network communications, the ISP delivers industry leading sensing technology for EnviZion and Pure-Flo hygienic diaphragm valves.

With an optional internal solenoid, commissioning the ISP couldn't be easier. A simple mounting configuration, auto calibration and continuous sensing make the ISP quick and reliable to install, calibrate and operate.

Constructed of highly durable, lightweight plastic with completely potted electronics, the ISP is well suited for typical industry washdowns.



ISP mounted on EnviZion valve

Features and Benefits

ISP Features


- Ultra-compact design
- Automatic calibration
- Optional diagnostics functionality
- 100% external calibration and solenoid override capabilities
- Reliable position sensing with non-contact magnetic resistance sensors
- Output/Bus Options: 2 wire, 3 wire, ASi, DeviceNet®
- High visibility LED lights
- Programmable open/closed LED color selections
- High strength, corrosion resistant polycarbonate and PES construction
- Potted electronics protected against moisture ingress and temporary immersion (IP67, Nema 4X rated)
- Integral solenoid valve option (Cv = 0.2)
- 1/8" NPT air connections (inlet, actuator, exhaust)
- M12 male quick connector standard
- Observation window (clear window to view actuator stroking)




Integrated Sensing Platform (ISP)



M12 Connector



Observation window



Calibration target



Dongle

ISP App Features

- iOS app for remote calibration of sensing positions
- Device Winking - determine location of device visually via blinking LED lights
- Cycle Counting - record number of open/closed cycles over date range or lifetime
- Valve data storage and retrieval for operating and maintenance history

A screenshot of the ISP app's 'Diagnostic Data' screen. It shows a table with valve position data, including stroke times for closed-to-open, open-to-closed, closed break, and open break, along with a cycle count and a reset button.

Diagnostic Data		
Valve Position		
Stroke Time	Baseline	Last
Closed-To-Open	2.86s	2.86s
Open-To-Closed	2.12s	2.12s
Closed Break	2.69s	2.69s
Open Break	1.92s	1.92s
Cycle Count:	32	Reset Count

ISP App diagnostic data



Dimensions


Ultra-Compact Design

The ISP features an ultra-compact design that allows for the utmost in installation flexibility. The ISP can be adapted to the entire range of ITT actuators from fractional (.25, .375, 0.5) through 4" valves.

The ISP design utilizes a fully potted base module. This module is adapted to the specific actuator based on type and size. The fractional (.25, .375, 0.5) through 1" valves require no mounting plate. The 1.5 – 2" valves require a 0.62" tall mounting plate. The 3" and 4" valves require a mounting plate and module with an extended dome to accommodate longer valve strokes. 0.75 and 1" ACS actuators require a mounting plate.

ISP Modular Mounting System

The ISP modular mounting system is designed to minimize overall valve installation height and to keep electronic module inventory to a minimum. The system uses two modules, a low profile version for use on the fractional (.25, .375, 0.5) through 2" valves and a tall version to accommodate the longer strokes of 3" and 4" valves.



Valve Size		Overall Height (A)	
Inch	DN	Inch	mm
BioviZion – 1" ¹	DN6-DN25	1.20	30.5
1.5 – 2"	DN40-DN50	1.95	50
3 – 4"	DN80-DN100	2.93	74.4

¹0.75 & 1" ACS require a mounting plate

Note: See Installation, Operation and Maintenance manual for mounting kit details and part numbers.


Sensing and Control

Reliable Position Sensing

ISP position sensing employs cutting edge magnetoresistive technology that maximizes position feedback accuracy and reliability. This technology draws little power and is particularly resistant to the effects of temperature change. The use of this proven technology results in the ISP being best in class in accuracy, power consumption and overall size.

Features and benefits:

- Non-contact sensors provide extended service life.
- Highly accurate over wide temperature ranges
- Open and close position are automatically calibrated
- Deadband is automatically adjusted based on valve stroke length
- Electronics are completely potted to protect against moisture and vibration
- Calibration is initiated with a magnetic dongle; no entry into the module is required



Integrated Pneumatic Control

The ISP features optional integrated control capability within the same footprint as the base module. There is no requirement for a bulky external solenoid that takes up precious space in the process system. An optimized solenoid with a Cv of 0.2 GPM draws 0.9W of power to operate valves quickly and efficiently. This allows valve response time to be minimized while a full complement of field devices can be powered by the network. Modules supplied with an internal solenoid can be operated as standard by the magnetic dongle or optionally with the ISP app.

Approximate Opening Times w/ Integral ISP (SV) Solenoid

Valve Sizes	Size Range	Typical Time (Seconds)
0.25 – 2"		<2
2.5 – 4"		5 – 10


Note: opening times depend on a variety of factors including actuator configuration, air line piping and process line conditions. Your results may vary.

ISP Outputs & Network Options

Discrete	Network
2 Wire	Asi 3.0
3 Wire	DeviceNet

Sensor Specifications for ISP with 3-Wire Discrete

Specifications	Notes
Configuration	(2) Discrete N.O. Push-Pull Input. Self-learning outputs ¹ for NPN/PNP/Sinking/Sourcing PLC input cards. (0 or 1) Integral Solenoid(s). Self-learning control input ¹ for NPN/PNP/Sinking/Sourcing PLC output cards.

Sensor Specifications	Notes	Minimum	Typical	Maximum	Units
Operation	Normally Open (solid state)				
Supply Voltage range		18	24	30	V
Operating Current	Supply = 24V, 1 LED Color ON, Solenoid OFF Supply = 24V, 1 LED Color ON, Solenoid ON		20 65		mA
Operating Supply Power	Supply = 18-30V, 1 LED Color ON, Solenoid OFF Supply = 18-30V, 1 LED Color ON, Solenoid ON			0.6 1.8	W
"Make" deadband	From Closed Set Point From Open Set Point		25 40		% Full Stroke
Connector	5 Pin M12 Male A-coded	5-PIN MICRO CONNECTOR (M12)  MALE (PINS)			
	Pin 1: 24V+ (L+) Pin 2: Open Signal (DI) Pin 3: 24V- (L-) Pin 4: Closed Signal (DI) Pin 5: Solenoid Signal (DO)				


Discrete Inputs	Notes	Maximum	Units
"No Load" Protection	Yes, Protected from direct application of 30 VDC all pins	Continuous	Minutes
PLC Card Compatibility	Self-learning outputs ¹ (inputs to PLC) configure themselves to the card used, whether it be PNP/NPN/Sinking/Sourcing, as long as the Minimum On state current rating is met.		

¹Patent Pending

Sensor Specifications for ISP with AS-Interface

Specifications	Notes
Communication Protocol	AS-Interface v3.0
Configuration	(2) Discrete Inputs, 62 Devices per network (0 or 1) Integral Solenoid(s)

Environmental Specifications	Maximum
Ingress Protection Degree	IP67
Location	Indoor


Sensor Specifications	Notes	Minimum	Typical	Maximum	Units
Supply Voltage Range	Use ASi Power Supply	26.5	30.55	31.6	V
Operating Current	1 LED Color ON, Solenoid OFF, Over Voltage Range 1 LED Color ON, Solenoid ON, Over Voltage Range		23 65		mA
"Make" deadband	From Closed Set Point From Open Set Point		25 40		% Full Stroke
Connector	4 Pin M12 Male A-coded	4-PIN MICRO CONNECTOR (M12)  MALE (PINS)			
	Pin 1: ASi + Pin 2: not used Pin 3: ASi – Pin 4: not used				
Manual Solenoid Override	On all -SV models: Local Latching Solenoid Override. On models with -SV and -BT: Temporary Solenoid Overrides via the ISP app. Overrides are automatically de-activated when disconnecting from the unit.				

Pneumatics Specifications

ISP With Pneumatics	
Manual override	Via Dongle, ISP App, PLC Output protocol (see Installation, Operation and Maintenance manual)
Configuration	Single pilot 3-way, 2-position, spring return
Flow Rating	0.2 Cv (Kv = 0.17 based on flow m3/hr)
Porting	1/8" NPT (Torque 5ft-lb recommended; 10ft-lb Max.)
Medium	Air or inert gas
Medium Temp. Range (TS)	-10°C to 50°C (14°F to 122°F)
Operating Pressure	25 psi to 120 psi (1.72 to 8.2 bar)
Operating Temperature	-10°C to 50°C (14°F to 122°F)
Operating Life	1,000,000 cycles
Type	Direct acting
Solenoid	
Operating Voltage	24V typical (see Installation, Operation and Maintenance manual)
Operating Temperature	-10°C to 50°C (14°F to 122°F)
Filtration Requirements	40 microns

VALVE SCHEMATIC

Single Pilot Spring Return Actuator



Notes:

- It is recommended to use thread tape etc. on fittings for the (S) and (A) 1/8" NPT ports.
- It is recommended that the exhaust port E be fitted with low restriction mufflers or breather vent caps or elbows etc. to prevent ingestion of water and debris into the pneumatic valve.

Calibration

Automatic Calibration

The intelligent sensing system offers precise feedback. Set up is accomplished in under one minute. Calibration can be accomplished with the dongle or via the ISP app.

Dongle Calibration

The ISP uses a dual action set-up to avoid unintended calibration.




Dongle

- A magnetic dongle is required to access control and calibration features
- LED feedback indicates calibration and solenoid over ride conditions
- ISP programming automatically sets open and closed positions

Calibration with ISP App Option

Remote calibration of valves is quick and easy with the ISP app option. An ISP with Bluetooth connectivity can be accessed from up to 33 feet (10 meters) away. Calibration and solenoid operation can be controlled through the app.




ISP app


ISP App Features and Benefits

- Safely control hard to reach valves without putting mechanics at risk
- Access factory preset tags and serial numbers remotely
- Electronically enter and store key valve tag numbers and maintenance logs
- Reduce network commissioning by accessing the network address and baud rate to make changes
- Reduce overall maintenance time by monitoring valve and diaphragm cycle count, cycle times and maintenance logs.
- Retrieve connected installation manuals


Diagnostics



- Customize tags
- Change addresses
- Force solenoids (on/off)
- Wink the ISP module
- Initiate calibration



- Store and view additional customized information
- Connect to installation manuals
- Link to website



- View real time valve position
- View lifetime cycles
- View resettable cycle count
- Monitor ISP temperature
- Record error status

Interfacing Devices:

iPhone Version 4s and above, iPad Version 3.0 and above, iPad mini all versions. Operating System iOS 9 or above.

Set Up and Operation

ISP modules with diagnostics can be commissioned by conventional AS-Interface or DeviceNet programming or with conventional power source and the ISP app on standard iOS devices. Diagnostic features include:

- All powered and in range ISP units will be identified.
- A specific ISP can be remotely identified with the Wink feature, automatically calibrated, and solenoid (if equipped) can be toggled on and off.
- Once connected switch settings/status, solenoid status and operation, and diagnostic information can be accessed and open data fields can be modified.
- Remote calibration, solenoid override and addressing from the ISP app are locked when network communication is functioning.
- Allows quick commissioning as electronic tags, model numbers, serial numbers and diagnostic data can be coordinated with standard CSV/Excel files.
- Overall maintenance safety and speed of commissioning is greatly improved by keeping personnel on the ground.
- Access to IOMs and website



EnviZion Valve

ISP Augments EnviZion Premium Valve Performance

The Biopharm industry relies on hygienic diaphragm valves for demanding process applications due to their unique balance of clean-ability, drain-ability and pressure/temperature capability. With the introduction of the EnviZion valve, ITT has set a new standard for the performance of the most common type of valve used in the industry. The EnviZion valve specifically helps customers install, operate, and maintain their valves more efficiently. This unique design provides a significant reduction in total cost of ownership while supporting the industries' goals to increase productivity, improve reliability and assure clean-ability.

Further enhancing EnviZion valve performance, the Integrated Sensing Platform (ISP) delivers unparalleled position sensing for the most critical, automated valves. With internal solenoid, auto calibration, and a wide array of output/bus options, combining the EnviZion valve with the ISP yields the most advanced valve technology in the industry today. With advantages in installation, calibration, cleanability, operation and maintenance, no other automated valve assembly matches the EnviZion valve and ISP sensing module. Specify the EnviZion valve and ISP sensing module. Specify the EnviZion and ISP together to bring this high performing technology to your operations and experience the benefits.



TOOL-LESS
ASSEMBLY



QUICK
CHANGE
BONNET



INTELLIGENT
AUTOMATION



CONTAMINATION
FREE



SEALING SYSTEM
3RD PARTY
CERTIFIED



LEAK FREE
SEAL INTEGRITY



FASTENER FREE



ACTIVE
360°
SEAL

ZERO
RETORQUES

How to Order

Model codes are shown below. Here are some examples of how model numbers are constructed:

- 3 Wire, no solenoid, 0.25"-2" cover size, no diagnostics: ISP-3W
- 3 wire, with solenoid, 0.25"-2" cover size, with diagnostics: ISP-3W-SV-BL
- ASi, no solenoid, 2.5"-4" cover size, no diagnostics: ISP-AI-LS
- ASi, with solenoid, 0.25"-2" cover size, with diagnostics and control: ISP-AI-SV-BT

Product		Output		Solenoid		Cover Size		Diagnostics	
Code	Option	Code	Option	Code	Option	Code	Option	Code	Option
ISP	ASi	AI	None	-	0.25"-2"	-	None	-	-
	2 Wire	2W	Included	SV	2.5"-4"	LS	With Diagnostics	BL	
	3 Wire	3W					With Diagnostics and Control	BT	
	DeviceNet	DN							



ENGINEERED FOR LIFE

ITT Engineered Valves
33 Centerville Road
Lancaster, PA 17603, USA
Tel: +1 (717) 509-2200

Cam-Line, Cam-Tite, Dia-Flo,
EnviZion, Pure-Flo, Skotch

ITT Engineered Valves
1110 Bankhead Avenue
Amory, MS 38821, USA
Tel: +1 (662) 256-7185

Fabri-Valve

ITT Industries Ltd.
Weycroft Avenue,
Millwey Rise Industrial Estate
Axminster, EX13 5HU, United Kingdom
Tel: +44 1297-639100

EnviZion, Pure-Flo

