

GE Oil & Gas

Masoneilan* Products

SVI II ESD

The first SIL3 Smart ESD device that is live during and after a shutdown



imagination at work

Bringing Plant Safety & Integrity to a Whole New Level

What is a SMART Shutdown Device?

The Masoneilan SVI II ESD Device from GE Oil & Gas incorporates the latest technology in emergency shutdown valve automation and in-service valve partial stroking, and it is designed using the proven electronic, pneumatic and non-contact technology from the SVI II AP valve positioner. SIL3 (Safety Integrity Level 3) compliant in accordance with IEC61508 per TUV and EXIDA, the SVI II ESD is suitable for use in safety instrumented functions.

The designated function of the SVI II ESD can be implemented by using a 4/20mA signal, 0-24Vdc or a combination of both. The single 4/20mA solution is SIL3 while at 4mA, allowing the device to execute the safety function while still being active. Key benefits of this approach include capturing shutdown events as a full-proof test, allowing continuous HART communications


during a trip, providing local panel annunciation, confirming ESD operations, and using the built-in discrete outputs .

This single 4/20mA solution provides ESD function and PST (Partial Stroke Test) function on a single wire pair. This enables:


- Reduced installation cost
- Execution of ESD valve PST from any logic solver

Automatic analysis of the ESD Valve yields additional benefits:

- Software automatically captures PST signatures
- Integration of diagnostics with logic solvers
- High diagnostic coverage factor



ESD Partial Stroke Signature Data



ESD Shutdown Signature

T = 0 sec: Safety Demand Initiated To Close Valve

What is SIL?

SIL, or Safety Integrity Level, is a standard governed by the International Electrical Committee (IEC). Its purpose is to:

- Establish risk reduction requirements
- Set probabilistic limits for hardware random failure
- Establish engineering procedures to prevent systematic design errors

Safe Failure Fraction and SIL - Type A

Solenoid Solutions Two (2) or More For SIL3 with a Low SFF

One (1) SVI II ESD Provides High SIL and High SFF

Safe Failure Fraction (SFF)	Hardware Fault Tolerance (HFT)		
	0	1	2
< 60%	SIL 1	SIL 2	SIL 3
60% < 90%	SIL 2	SIL 3	SIL 4
90% < 99%	SIL 3	SIL 4	SIL 4
> 99%	SIL 3	SIL 4	SIL 4


SVI II ESD: Designed Exclusively for ON/OFF ESD Valve Applications

The innovative SVI II ESD design provides a designated safety function completely independent from the partial stroke testing function. The design architecture, which separates the embedded microprocessor and the safety shutdown circuitry, offers a sophisticated platform while being Type A (simple device) compliant.

As a smart ESD valve device with partial stroking functionality, the SVI II ESD includes self-diagnostics and is designed to announce a fault through its built-in digital output (DO) and by using the HART protocol. Four possible launching methods for partial stroke testing (PST) are built in. For safety instrumented systems usage it is assumed that annunciation is performed through the built-in digital output or by using the HART protocol. The safety input can either be a 4/20mA current loop (trip when current $\leq 5.6\text{mA}$) or a 24Vdc discrete input (trip on $< 3\text{Vdc}$). Power to the unit is supplied by the 4/20mA current loop, except in a two-wire discrete input configuration, in which the power is supplied by the 24V input.

- The SVI II ESD is unique in that it is SIL3 at 4mA⁽¹⁾ and therefore allows the built-in microcontroller to capture HART diagnostics whenever the safety function is engaged. Compare that to the current standard approach, which requires the signal to be 0mA to provide a safety function with an SIL3 compliance. Such solutions do not allow the microprocessor to be available and active during a shutdown event.
- Furthermore, the SVI II ESD has a configurable latching feature whenever a trip occurs.

⁽¹⁾ Suitable with ASD and A/DSD models.



SVI II ESD operating on a quarter turn ESD valve with NAMUR VDI/VDE 3845 mounting kit

Safety Function/PST/Diagnostic on One-Wire Pair

Integration shown with a typical Logic Solver and HART® Analog Output Card.




Logic Solver

ValVue* ESD Features

- ESD health monitoring
- PST auto-archiving
- Full-proof testing
- Setup / commission / diagnose

ESD Signal
HART Diagnostics
Analog PST⁽¹⁾



Embedded local control panel

LCD display and three explosion proof push-buttons for:

- Valve Configuration and Calibration
- Local PST⁽¹⁾
- PST, Safety Trip and Device Status
- Position Feedback

70+ ESD Warnings

7-Language Display

English, French, German, Italian,
Japanese, Portuguese, Spanish

Alternating Readings of Dynamic Variables

Safety Demand Signal Strength


⁽¹⁾ Analog PST is patent pending.

SVI II ESD Device Models and Safety Demand Implementation

No Solenoid Required


Two-Wire Analog Safety Demand (ASD)

This ASD model utilizes a 4/20mA signal, where the safety function of de-energizing the pneumatic actuator is achieved with a value of <5.6mA. This adds novel solution value as it simplifies product implementation.




Two-Wire Discrete Safety Demand (DSD)

This DSD model utilizes a 0-24Vdc signal where the safety function of de-energizing the pneumatic actuator is achieved with a value of <3Vdc. This solution is well-suited when retrofitting an actuator fitted with a 24Vdc solenoid.



Four-Wire Analog Setpoint with Discrete Safety Demand (A/DSD)

This A/DSD model utilizes the 4/20mA to position the valve (Open or Closed), allow for HART communications and start a PST using specific analog signal while a separate 0-24Vdc signal provides the safety function of de-energizing the actuator.




⁽¹⁾ The SVI II ESD provides On/Off valve positioning. Throttling capability is available in manual mode only through HART communication or local pushbuttons.

ESD Valve Diagnostics With ValVue ESD Software

The SVI II ESD is equipped with one non-contact travel sensor, five pressure sensors, one temperature sensor, and one loop current sensor. Therefore, it can diagnose the health of the valve as well as monitor its various sub-components in real time.


The SVI II ESD provides more than 70 possible alarms/warnings including:

- Valve Stuck Open/Closed
- Feedback Linkage Drift
- Pneumatic Train Integrity
- Air Supply Low/High
- Breakout Force Exceeded



User friendly dashboard of ESD Valve condition.

The database-driven companion software, ValVue ESD, continuously monitors the health of the ESD valves and provides a global view of the health of all compatible ESD valves in a plant. That facilitates the planning and resources to properly maintain ESD valves. ValVue ESD software provides for the SVI II ESD setup, device alarms, PST settings, partial stroke test execution and monitoring of the installed base of ESD valves. The PST signatures are automatically stored in the software database with the built-in PST Monitor. Additionally, the software allows for proof testing signatures and stroking speed calculation signatures. The diagnostic analysis is graphically plotted over time to help operators easily identify performance degradation.



Full valve signature with valve/actuator friction, spring range and calibration, seating analysis and response time.

Broad Launch Capabilities

The SVI II ESD includes broad PST-launching capabilities including the following standard features:

- Local using the LCD display, or using a local panel wired in-line with SVI II ESD
- Remote using HART® capable interfaces
- Remote using a specific analog signal (ASD and A/DSD models only)
- Automated with the built-in scheduler

The SVI II ESD automatically captures the PST in its non-volatile memory and stores the analysis. Two signatures can be stored, allowing the PST Monitor functionality with ValVue ESD software to automatically synchronize its database with the field data. This software can stand alone or be integrated.

PST Parameters

Since the SVI II ESD contains the settings to execute a PST in its non-volatile memory, the PST is reliably executed regardless of the launching method. The parameters include boundaries to prevent undesirable valve movements during a partial stroke test.

PST Launching Methods	
Analog Loop Current (Patent Pending)	
Local Button	
Built-In Scheduler	
Host System via HART (EDDL, DTM or ValVue ESD)	
HART Field Calibrators	


Partial Stroke Test Overview

PST Implementation Benefits with SVI II ESD Device Technology


Integrated	The test and the results are integrated with the rest of the safety system.
Automated	Per IEC61511 requirements, PST execution can be fully automated, which reduces the risk of human error. Test results are stored in the memory of the SVI II ESD and automatically communicated to the user, providing actionable information about potential valve performance problems.
Versatile and Accessible	PSTs from the SVI II ESD can be safely executed locally or remotely, and the results accessed from the logic solver.
User Friendly	Tests are easy to execute and the results are easy to understand. The user does not need to be an expert on ESD valves or digital shutdown devices to complete the test and interpret the results.

Partial Stroke Test Signature and Plotting Travel vs. Actuator Pressure


Smart partial stroke testing allows reliable testing of emergency shutdown valves and provides greater diagnostic coverage



PST signature shown over 20% travel





Plotting travel and actuator pressure vs time




Automated Emergency Shutdown Signature

Emergency Shutdown Signature

The SVI II ESD Device is the first SIL3-rated product capable of capturing a shutdown event during a trip using a single-wire pair⁽¹⁾. This feature captures the shutdown event in non-volatile memory, which allows the safety event to be investigated and a complete proof test to be conducted. Therefore, this proof test is automatically documented and the next proof test can be rescheduled according to the required probability of failure on demand (PFD). ^{(1) Suitable with ASD model only.}



Event Timeline With and Without PST and With Shutdown Event Capture



	Example 1	Example 2	Explanation
# Of Shutdowns for Proof Testing	4	2	The mandatory testing of ESD valves requires process downtime
Cost Per Shutdown	\$500,000	\$500,000	Average cost of shutdown including loss of production
Possible Shutdown Costs	\$2,000,000	\$1,000,000	
Savings	-	\$1,000,000	

Applications and Specifications

Inputs/ Outputs	Model ASD (Analog Safety Demand)	Model DSD (Discrete Safety Demand)	Model A/DSD (Analog Power with Discrete Safety Demand)
Analog In (4/20mA)	Safety Trip Trigger + HART® + Analog PST	-	Device Power + Analog PST + HART
ESD In (0-24Vdc)	-	Safety Trip Trigger + HART	Safety Trip Trigger
Analog Out (4-20mA)	Position Transmitter		
Switch1 (1A, 24Vdc)	ESD Status		
Switch2 (1A, 24Vdc)	Configurable Status ⁽³⁾		
DI (switch input)	Unlatch the SVI II ESD ⁽¹⁾		
PV (1-5Vdc)	Read Tight Shutoff Flow ⁽²⁾		
Local LCD / Buttons	Device Configuration and Calibration, ESD Status PST Configuration Local PST Execution		

The use of HART or the ESD status switch provide ESD valve and SVI II ESD diagnostics which are necessary to claim PFD improvements.

- ⁽¹⁾ The latching function is software configurable.
- ⁽²⁾ This variable is sent via HART Command 3 as a tertiary variable
- ⁽³⁾ The switch can be configured as:
 - Normally Open (NO) or Normally Closed (NC)

The switch can be configured to alert if one of the following events occurs:

- PST in progress
- ESD triggered
- ESD fault annunciation
- Position low limit
- Position high limit
- Failsafe
- Normal mode
- Manual or Out-Of-Service mode

IEC61508 certified TUV
 Type A device (simplex, low demand)
 SIL3 safety shutdown function
 Safe failure fraction with PVST up to 99% upon model

Performance

Hysteresis + deadband $\pm 0.3\%$
 Operating temperature range -40°C to $+85^{\circ}\text{C}$
 (-40°F to $+185^{\circ}\text{F}$)

Input power and signal

ASD & A/DSD signal 4/20mA with HART®
 Communication protocol
 Power supply taken from 4/20mA control
 Signal (ASD, A/DSD)
 Power supply taken from 24Vdc signal (DSD)
 Minimum terminal voltage 9.5Vdc @ 20mA
 Safety function: $< 5.6\text{mA}$ (model ASD)
 $< 3\text{Vdc}$ (A/DSD or DSD)
 Energized output: $> 15\text{mA}$ (ASD,A/DSD),
 $> 15\text{Vdc}$ (DSD)
 ESD IN current draw $< 9.5\text{mA}$ (DSD, A/DSD)
 HART over 4/20mA signal (ASD,A/DSD)
 HART over 24Vdc signal (DSD, requires signal
 conditioner)

Pneumatics

Regulated and filtered air required
 Single acting: supply pressure 30-120 psi max
 (2.1-7.8 bar).
 Air supply regulated 10 psi above actuator
 spring range.
 Air delivery:
 325 NI/min (11.55 scfm) at 2.1 bar (30psi) supply
 765 NI/min (27 scfm) at 6.2 bar (90 psi) supply
 Air consumption 5.7 NI/min (0.2 scfm) at 2.1 bar
 (30 psi) supply
 $C_v=0.53$ (venting) $C_v=0.57$ (filling)

Control valve mounting system

Non-contact hall effect position sensor (18° to
 140° rotation)
 Rotary NAMUR mounting kit per VDI/VDE 3845
 Reciprocating kits available
 Compliance with field calibrators with HART®
 protocol such as GE Druck DPI620 and others

System integration

Device description (EDDL or DTM)
 ValVue ESD application
 ValVue ESD PRM plug-in
 Interoperability with many FDT/DTM and eDDL
 capable hosts

ESD and diagnostic capabilities

IEC61508 compliant up to SIL3 certified by TUV
 and EXIDA
 Partial stroke testing initiation (HART, analog,
 local pushbutton, built-in scheduler)
 Digital output for PST results and
 SVI II ESD health
 Non-volatile memory for two (2) PST signature
 Non-volatile memory for ESD shutdown event
 signature
 Safety trip trigger: 4/20mA or 24Vdc input
 Local PST scheduler with built-in calendar
 Full stroke valve signature & positioner
 diagnostics
 Built-in explosion proof external LCD with
 pushbuttons
 Language support:
 English Japanese
 French Portuguese
 German Spanish
 Italian

Compliance with ANSI/API 754 specification

Process Safety Performance Indicators for the
 Refining and Petrochemical Industries



Hazardous area certifications

Enclosure rating NEMA 4X / IP 66
 Low copper aluminum or 316L housing
 Red electrical cover and housing for clear
 identification as a safety related device

ATEX approvals:

Intrinsic safety
 Gas: II 1G Ex ia IIC T6 / T5 / T4
 Dust: II 1D Ex iaD A20 T96°C
 Flameproof
 Gas: II 2G Ex dm IIB + H2 T6 / T5 / T4
 Dust: II 2D Ex tD A21 IP66 T96°C
 Energy limited
 Gas: II 3G Ex nL IIC T6 / T5
 Dust: II 3D Ex tD A22 IP66 T96°C
 Approval standards:
 EN60079-0:2006, EN60079-1:2007, EN60079-
 11:2007, EN60079-15:2005, EN60079-18:2004,
 EN60079-26:2007, EN61241-0:2006, EN61241-
 1:2004, EN61241-11:2006, EN61241-18:2004,
 EN1127-1:2007, EN60529:1991

CSA international certifications:

Explosion proof
 CL I; Div. 1; GR B, C, D T6 / T5 / T4
 Dust ignition proof
 CL II/III; Div. 1; GR E, F, G T6 / T5 / T4
 Certified CL II; Div. 2; GR F, G
 Certified CL III; Div. 2
 Certified CL I; Div. 2; GR , B, C, D
 Intrinsically safe
 CL I, II, III; Div. 1; GR A, B, C, D, E, F, G T6 / T5 / T4
 Approval standard: CAN/CSA-C22.2 #
 94-M91,142-M1987, 157-92, 213 M1987,60529:05

FM approvals:

Explosion proof
 CL I; Div. 1; GR B, C, D T6 / T5 / T4
 Dust ignition proof
 CL II/III; Div. 1; GR E, F, G T6 / T5 / T4
 Suitable for CL II, III; Div. 2; GR F, G
 Non-incendive CL I; Div. 2; GR A, B, C, D
 Intrinsically safe
 CL I, II, III; Div. 1; GR A, B, C, D, E, F, G
 Approval standards: Class 3600, 3615, 3810,
 ANSI/NEMA 250, IEC 60079-18 IEC60529 +A1

IECEx approvals:

Intrinsically safe
 Ex ia IIC T6
 Explosion proof
 Ex d mb IIC Gb T5
 Ex tD A21 IP66 T96°C; Ta= -40°C to $+85^{\circ}\text{C}$
 IP66

Temperature class:

T6 = 60°C (160°F), T5 = 75°C (167°F),
 T4 = 85°C (185°F)

Immunity performance:

EN61000-4-2, -3, -4, -5, -6, -8
 EMC per IEC61514-2, 61326, 61326-3

Radiation performance:

CISPR 22

Other approvals:

INMETRO, KOSHA and NEPSI

How to Specify the SVI II ESD Device



Key Features:

- SIL3 While at 4mA
- Shutdown Event Captured
- Automatic Analysis of ESD Valve Health



Base Model Number

SVI II ESD - 6



SVI II ESD - 6

b

c

d

e

f

g

h

Customer must select one item from each category



DIRECT SALES OFFICE LOCATIONS

AUSTRALIA

Brisbane
Phone: +61-7-3001-4319
Fax: +61-7-3001-4399

Perth
Phone: +61-8-6595-7018
Fax: +61-8-6595-7299

Melbourne
Phone: +61-3-8807-6002
Fax: +61-3-8807-6577

BELGIUM
Phone: +32-2-344-0970
Fax: +32-2-344-1123

BRAZIL
Phone: +55-11-2146-3600
Fax: +55-11-2146-3610

CHINA
Phone: +86-10-8486-4515
Fax: +86-10-8486-5305

FRANCE
Courbevoie
Phone: +33-1-4904-9000
Fax: +33-1-4904-9010

GERMANY
Ratingen
Phone: +49-2102-108-0
Fax: +49-2102-108-111

INDIA
Mumbai
Phone: +91-22-8354790
Fax: +91-22-8354791

New Delhi
Phone: +91-11-2-6164175
Fax: +91-11-5-1659635

ITALY
Phone: +39-081-7892-111
Fax: +39-081-7892-208

JAPAN
Chiba
Phone: +81-43-297-9222
Fax: +81-43-299-1115

KOREA
Phone: +82-2-2274-0748
Fax: +82-2-2274-0794

MALAYSIA
Phone: +60-3-2161-0322
Fax: +60-3-2163-6312

MEXICO
Phone: +52-5-310-9863
Fax: +52-5-310-5584

THE NETHERLANDS
Phone: +0031-15-3808666
Fax: +0031-18-1641438

RUSSIA
Veliky Novgorod
Phone: +7-8162-55-7898
Fax: +7-8162-55-7921

Moscow
Phone: +7 495-585-1276
Fax: +7 495-585-1279

SAUDI ARABIA
Phone: +966-3-341-0278
Fax: +966-3-341-7624

SINGAPORE
Phone: +65-6861-6100
Fax: +65-6861-7172

SOUTH AFRICA
Phone: +27-11-452-1550
Fax: +27-11-452-6542

SOUTH & CENTRAL
AMERICA AND THE CARIBBEAN
Phone: +55-12-2134-1201
Fax: +55-12-2134-1238

SPAIN
Phone: +34-93-652-6430
Fax: +34-93-652-6444

UNITED ARAB EMIRATES
Phone: +971-4-8991-777
Fax: +971-4-8991-778

UNITED KINGDOM
Wooburn Green
Phone: +44-1628-536300
Fax: +44-1628-536319

UNITED STATES
Massachusetts
Phone: +1-508-586-4600
Fax: +1-508-427-8971

Corpus Christi, Texas
Phone: +1-361-881-8182
Fax: +1-361-881-8246

Deer Park, Texas
Phone: +1-281-884-1000
Fax: +1-281-884-1010

Houston, Texas
Phone: +1-281-671-1640
Fax: +1-281-671-1735



www.geoilandgas.com/valves

* Masoneilan, SVI and ValVue are registered trademarks of the General Electric Company. Other company names and product names used in this document are the registered trademarks or trademarks of their respective owners.

© 2012 General Electric Company. All rights reserved.

GEA19512 12/2012